

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264348

Luminaire Tested: **LD2B10D010 EU2B1010SP159035 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159035 2LBDC*MB
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.0 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264348

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264348

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3633314
5°	2912296
10°	1271118
15°	393903
20°	137294
25°	60642
30°	27459
35°	14274
40°	8115
45°	3837
50°	2456
55°	1376
60°	789
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264348

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.6	58.0
10°-20°	244.6	31.8
20°-30°	55.7	7.2
30°-40°	16.0	2.1
40°-50°	5.0	0.6
50°-60°	1.5	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.9	97.0
0°-40°	762.9	99.1
0°-60°	769.3	99.9
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7364	
5°	5880	447
15°	771	245
25°	111	56
35°	24	16
45°	6	5
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264348

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	7364.4
1°	7272.8
2°	7082.3
3°	6786.8
4°	6380.7
5°	5880.5
6°	5267.3
7°	4582.2
8°	3867.1
9°	3174.9
10°	2537.3
11°	1997.6
12°	1572.4
13°	1237.4
14°	977.4
15°	771.2
16°	608.4
17°	484.4
18°	389.6
19°	316.9
20°	261.5
22.5°	169.1
25°	111.4
26°	94.0
27°	79.8
28°	67.2
29°	56.1
30°	48.2
32.5°	33.2
35°	23.7
37.5°	17.4
40°	12.6
42.5°	8.7
45°	5.5
47.5°	4.0
50°	3.2
52.5°	2.4
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8



TEST NUMBER: P264348

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)