

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224947

Luminaire Tested: **LD2B15D010 EU2B15FL408030 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408030 2LBD*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.6 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224947

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224947

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100		108	104	101	99		101	99	97			98	96	94			96
3	106	100	96	93		104	99	95	92		97	94	91			94	92	90			92
4	102	96	91	88		100	94	90	87		92	89	86			91	88	85			89
5	98	91	86	83		96	90	86	82		89	85	82			87	84	81			86
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75		90	83	78	75		82	77	74			80	77	74			79
8	88	80	75	72		87	79	75	72		78	74	71			77	74	71			77
9	85	77	72	69		84	76	72	69		75	71	68			75	71	68			74
10	82	74	69	66		81	73	69	66		73	69	66			72	68	66			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1275918
5°	1249219
10°	1100199
15°	863174
20°	573212
25°	329047
30°	165042
35°	76225
40°	30996
45°	13859
50°	7231
55°	4525
60°	2092
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224947

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.4	21.3
10°-20°	582.6	42.4
20°-30°	362.0	26.3
30°-40°	109.2	7.9
40°-50°	22.3	1.6
50°-60°	5.8	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1238.0	90.0
0°-40°	1347.2	97.9
0°-60°	1375.3	100.0
0°-90°	1375.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3294	
5°	3213	293
15°	2152	583
25°	770	362
35°	161	109
45°	25	22
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224947

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3294.0
1°	3283.4
2°	3268.7
3°	3258.0
4°	3242.1
5°	3212.8
6°	3166.1
7°	3102.2
8°	3010.3
9°	2906.4
10°	2797.2
11°	2681.3
12°	2560.1
13°	2433.5
14°	2295.0
15°	2152.5
17.5°	1770.2
20°	1390.6
22.5°	1054.9
25°	769.9
27.5°	543.5
30°	369.0
32.5°	242.4
35°	161.2
37.5°	99.9
40°	61.3
42.5°	40.0
45°	25.3
47.5°	16.0
50°	12.0
52.5°	8.0
55°	6.7
57.5°	4.0
60°	2.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224947

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)