

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224409

Luminaire Tested: **LD2B15D010 EU2B15FL409730 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409730 2LBDSQC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1019.1 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224409

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224409

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			85
6	94	87	82	78		93	86	81	78		84	80	77			83	80	77			82
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	922619
5°	905808
10°	805208
15°	633275
20°	421397
25°	241945
30°	122194
35°	57500
40°	23159
45°	11449
50°	6327
55°	4390
60°	4028
65°	2383
70°	2945
75°	1946
80°	2900
85°	0



TEST NUMBER: P224409

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.4	20.9
10°-20°	427.8	42.0
20°-30°	266.1	26.1
30°-40°	81.8	8.0
40°-50°	18.0	1.8
50°-60°	6.4	0.6
60°-70°	3.2	0.3
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.2	89.0
0°-40°	989.1	97.1
0°-60°	1013.5	99.4
0°-90°	1019.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2382	
5°	2330	213
15°	1579	428
25°	566	266
35°	122	82
45°	21	18
55°	6	6
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224409

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2381.9
2.5°	2371.4
5°	2329.6
7.5°	2223.7
10°	2047.2
12.5°	1835.4
15°	1579.2
17.5°	1299.4
20°	1022.3
22.5°	775.2
25°	566.1
27.5°	398.7
30°	273.2
32.5°	184.3
35°	121.6
37.5°	73.2
40°	45.8
42.5°	31.4
45°	20.9
47.5°	14.4
50°	10.5
52.5°	9.2
55°	6.5
57.5°	5.2
60°	5.2
62.5°	3.9
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)