

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B1510NFL258050 2LBPINW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510NFL258050 2LBPINW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
ROUND PINHOLE WHITE OCULUS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1191.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL258050 2LBPINW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL258050 2LBPINW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97		
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95		
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93		
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90		
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88		
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86		
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85		
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83		
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81		
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2796599
5°	2597006
10°	1765114
15°	583961
20°	198342
25°	100473
30°	51902
35°	17029
40°	6323
45°	3452
50°	965
55°	1081
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL258050 2LBPINW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	567.2	47.6
10°-20°	473.8	39.8
20°-30°	114.6	9.6
30°-40°	29.6	2.5
40°-50°	4.9	0.4
50°-60°	0.9	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.7	97.0
0°-40°	1185.3	99.5
0°-60°	1191.0	100.0
0°-90°	1191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7217	
5°	6677	567
15°	1456	474
25°	235	115
35°	36	30
45°	6	5
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL258050 2LBPINW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7217.3
2.5°	7096.6
5°	6676.7
7.5°	5807.0
10°	4486.1
12.5°	2775.0
15°	1455.7
17.5°	786.6
20°	481.0
22.5°	332.2
25°	235.0
27.5°	166.1
30°	116.0
32.5°	81.5
35°	36.0
37.5°	15.7
40°	12.5
42.5°	9.4
45°	6.3
47.5°	3.1
50°	1.6
52.5°	1.6
55°	1.6
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)