

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B10WFL559040D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14811)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10WFL559040D010 2LBDC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 823.2 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559040D010 2LBDC*MMS

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559040D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93						
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87						
3	102	96	91	87	100	94	90	86	92	88	84	89	86	83	87	84	82	80						
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74						
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69						
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65						
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60						
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56						
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53						
10	71	62	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393001
5°	389214
10°	361305
15°	317159
20°	272921
25°	232286
30°	183962
35°	127673
40°	81105
45°	48918
50°	27901
55°	15262
60°	1782
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559040D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.9	11.3
10°-20°	220.1	26.7
20°-30°	247.1	30.0
30°-40°	170.3	20.7
40°-50°	72.0	8.7
50°-60°	20.3	2.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.1	68.0
0°-40°	730.4	88.7
0°-60°	822.7	99.9
0°-90°	823.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	823.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1015	
5°	1001	93
15°	791	220
25°	544	247
35°	270	170
45°	89	72
55°	23	20
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559040D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1014.6
2.5°	1011.2
5°	1001.0
7.5°	969.4
10°	918.6
12.5°	856.4
15°	790.9
17.5°	722.0
20°	662.1
22.5°	604.5
25°	543.5
27.5°	480.2
30°	411.3
32.5°	336.7
35°	270.0
37.5°	211.3
40°	160.4
42.5°	120.9
45°	89.3
47.5°	64.4
50°	46.3
52.5°	33.9
55°	22.6
57.5°	11.3
60°	2.3
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)