

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264148

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264148

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264148

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6398458
5°	5128672
10°	2238446
15°	693671
20°	241826
25°	106804
30°	48366
35°	25115
40°	14362
45°	6768
50°	4298
55°	2408
60°	1381
65°	1634
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264148

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	786.4	58.0
10°-20°	430.7	31.8
20°-30°	98.2	7.2
30°-40°	28.2	2.1
40°-50°	8.7	0.6
50°-60°	2.6	0.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1315.2	97.0
0°-40°	1343.5	99.1
0°-60°	1354.8	99.9
0°-90°	1356.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12969	
5°	10356	786
15°	1358	431
25°	196	98
35°	42	28
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264148

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12969.1
1°	12807.6
2°	12472.3
3°	11951.8
4°	11236.6
5°	10355.8
6°	9275.9
7°	8069.5
8°	6810.1
9°	5591.2
10°	4468.2
11°	3517.8
12°	2769.1
13°	2179.1
14°	1721.3
15°	1358.1
16°	1071.5
17°	853.0
18°	686.0
19°	558.0
20°	460.6
22.5°	297.8
25°	196.2
26°	165.6
27°	140.5
28°	118.3
29°	98.8
30°	84.9
32.5°	58.4
35°	41.7
37.5°	30.6
40°	22.3
42.5°	15.3
45°	9.7
47.5°	7.0
50°	5.6
52.5°	4.2
55°	2.8
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4



TEST NUMBER: P264148

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBD*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)