

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223798

Luminaire Tested: **LSSQWM2B10SP159040D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP159040D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 434.9 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223798

CATALOG NUMBER: LSSQWM2B10SP159040D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223798

CATALOG NUMBER: LSSQWM2B10SP159040D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	116	114	112	111	113	112	110	109		108	107	106			104	103	103			101
2	113	110	107	105	111	108	106	104		105	103	102			102	101	100			100
3	110	106	103	101	108	105	102	100		102	100	98			100	98	97			98
4	108	103	100	97	106	102	99	97		100	98	96			98	96	95			97
5	105	101	97	95	104	100	97	94		98	96	94			97	95	93			95
6	103	98	95	93	102	98	95	92		96	94	92			95	93	91			94
7	101	96	93	91	100	96	93	90		95	92	90			94	91	90			93
8	100	94	91	89	99	94	91	89		93	90	89			92	90	88			92
9	98	93	90	88	97	92	89	87		92	89	87			91	89	87			90
10	96	91	88	86	96	91	88	86		90	88	86			90	87	86			89

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2089770
5°	1510704
10°	439812
15°	154309
20°	66076
25°	29746
30°	11495
35°	5722
40°	3843
45°	2465
50°	1386
55°	1013
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223798

CATALOG NUMBER: LSSQWM2B10SP159040D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.9	63.2
10°-20°	111.8	25.7
20°-30°	34.3	7.9
30°-40°	8.5	1.9
40°-50°	3.5	0.8
50°-60°	1.5	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	421.1	96.8
0°-40°	429.6	98.8
0°-60°	434.6	99.9
0°-90°	434.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	434.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5395	
5°	3885	275
15°	385	112
25°	70	34
35°	12	8
45°	4	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223798

CATALOG NUMBER: LSSQWM2B10SP159040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5395.1
1°	5312.7
2°	5111.6
3°	4791.1
4°	4372.2
5°	3885.3
6°	3336.4
7°	2740.7
8°	2136.6
9°	1571.8
10°	1118.2
11°	801.4
12°	602.6
13°	490.7
14°	429.4
15°	384.8
17.5°	237.4
20°	160.3
22.5°	107.4
25°	69.6
27.5°	42.3
30°	25.7
32.5°	16.6
35°	12.1
37.5°	9.8
40°	7.6
42.5°	6.0
45°	4.5
47.5°	3.0
50°	2.3
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223798

CATALOG NUMBER: LSSQWM2B10SP159040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)