

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559040D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10WFL559040D010 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 825.9 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559040D010 2LBDC*MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559040D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93						
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86						
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80						
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74						
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69						
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64						
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60						
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56						
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53						
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387423
5°	384937
10°	357883
15°	314151
20°	270819
25°	231602
30°	183783
35°	128098
40°	81055
45°	49465
50°	29226
55°	16005
60°	3486
65°	3116
70°	2605
75°	3442
80°	2454
85°	4889



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559040D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	11.1
10°-20°	218.2	26.4
20°-30°	246.2	29.8
30°-40°	170.3	20.6
40°-50°	72.6	8.8
50°-60°	21.0	2.5
60°-70°	3.1	0.4
70°-80°	2.0	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.2	67.3
0°-40°	726.5	88.0
0°-60°	820.1	99.3
0°-90°	825.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	825.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1000	
5°	990	92
15°	783	218
25°	542	246
35°	271	170
45°	90	73
55°	24	21
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559040D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1000.2
2.5°	999.1
5°	990.0
7.5°	959.6
10°	909.9
12.5°	848.9
15°	783.4
17.5°	715.7
20°	657.0
22.5°	601.7
25°	541.9
27.5°	478.6
30°	410.9
32.5°	337.5
35°	270.9
37.5°	210.0
40°	160.3
42.5°	120.8
45°	90.3
47.5°	65.5
50°	48.5
52.5°	35.0
55°	23.7
57.5°	10.2
60°	4.5
62.5°	3.4
65°	3.4
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)