

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264153

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBDC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1295.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264153

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264153

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	102		101	100	100
2	113	109	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	96	95
4	107	103	99	97		106	102	99	96		100	97	95		98	96	94		96	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	91
6	103	98	94	92		102	97	94	91		96	93	91		95	92	90		93	91	90
7	101	95	92	90		100	95	92	89		94	91	89		93	90	89		92	90	88
8	99	93	90	88		98	93	90	88		92	89	87		91	89	87		91	88	87
9	97	92	88	86		96	91	88	86		91	88	86		90	87	86		89	87	85
10	95	90	87	85		95	90	87	85		89	86	85		89	86	84		88	86	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6110582
5°	4897937
10°	2137751
15°	662463
20°	230958
25°	102014
30°	46201
35°	24031
40°	13718
45°	6489
50°	4068
55°	2322
60°	1283
65°	1518
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264153

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.0	58.0
10°-20°	411.3	31.8
20°-30°	93.8	7.2
30°-40°	27.0	2.1
40°-50°	8.3	0.6
50°-60°	2.5	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1256.1	97.0
0°-40°	1283.0	99.1
0°-60°	1293.8	99.9
0°-90°	1295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1295.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12386	
5°	9890	751
15°	1297	411
25°	187	94
35°	40	27
45°	9	8
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264153

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	12385.6
1°	12231.5
2°	11911.2
3°	11414.2
4°	10731.1
5°	9889.9
6°	8858.7
7°	7706.5
8°	6503.8
9°	5339.6
10°	4267.2
11°	3359.5
12°	2644.6
13°	2081.1
14°	1643.9
15°	1297.0
16°	1023.3
17°	814.6
18°	655.2
19°	532.9
20°	439.9
22.5°	284.4
25°	187.4
26°	158.1
27°	134.2
28°	113.0
29°	94.4
30°	81.1
32.5°	55.8
35°	39.9
37.5°	29.2
40°	21.3
42.5°	14.6
45°	9.3
47.5°	6.6
50°	5.3
52.5°	4.0
55°	2.7
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3



TEST NUMBER: P264153

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBDC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)