

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224913

Luminaire Tested: **LSR2B10FL409030D2WD010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10FL409030D2WD010 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 610.1 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224913

CATALOG NUMBER: LSR2B10FL409030D2WD010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224913

CATALOG NUMBER: LSR2B10FL409030D2WD010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	94		96	94	93
3	106	100	96	93		104	99	95	92		97	93	91		94	92	90		92	90	88
4	102	96	91	88		100	94	90	87		92	89	86		91	88	85		89	86	84
5	98	91	86	83		96	90	86	82		89	85	82		87	84	81		86	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		82	77	74		80	77	74		79	76	74
8	88	80	75	72		87	79	75	72		78	74	71		77	74	71		77	73	71
9	85	77	72	69		84	76	72	69		75	71	68		75	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	69	66		72	68	66		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565835
5°	553999
10°	487955
15°	382844
20°	254207
25°	145953
30°	73173
35°	33810
40°	13754
45°	6135
50°	3194
55°	2026
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224913

CATALOG NUMBER: LSR2B10FL409030D2WD010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	21.3
10°-20°	258.4	42.3
20°-30°	160.5	26.3
30°-40°	48.4	7.9
40°-50°	9.9	1.6
50°-60°	2.6	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.1	90.0
0°-40°	597.5	97.9
0°-60°	610.0	100.0
0°-90°	610.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	610.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1461	
5°	1425	130
15°	955	258
25°	342	161
35°	72	48
45°	11	10
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224913

CATALOG NUMBER: LSR2B10FL409030D2WD010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1460.8
1°	1456.2
2°	1449.7
3°	1444.9
4°	1437.8
5°	1424.8
6°	1404.2
7°	1375.8
8°	1335.1
9°	1289.0
10°	1240.6
11°	1189.1
12°	1135.4
13°	1079.3
14°	1017.8
15°	954.7
17.5°	785.1
20°	616.7
22.5°	467.9
25°	341.5
27.5°	241.0
30°	163.6
32.5°	107.5
35°	71.5
37.5°	44.3
40°	27.2
42.5°	17.8
45°	11.2
47.5°	7.1
50°	5.3
52.5°	3.6
55°	3.0
57.5°	1.8
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224913

CATALOG NUMBER: LSR2B10FL409030D2WD010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)