

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264830

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1422.9 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264830

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264830

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	106	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	91		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	88	85		90	87	85		89	86	84		88	86	84
8	95	89	86	83		94	89	85	83		88	85	82		87	84	82		86	84	82
9	93	87	83	81		92	87	83	81		86	83	81		85	82	80		85	82	80
10	91	85	82	79		91	85	81	79		84	81	79		84	81	79		83	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5023459
5°	4088605
10°	2208588
15°	880611
20°	353079
25°	169080
30°	87675
35°	46316
40°	25697
45°	15908
50°	10899
55°	7311
60°	5624
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264830

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	663.9	46.7
10°-20°	523.8	36.8
20°-30°	154.5	10.9
30°-40°	51.4	3.6
40°-50°	19.3	1.4
50°-60°	8.5	0.6
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1342.3	94.3
0°-40°	1393.7	97.9
0°-60°	1421.6	99.9
0°-90°	1422.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1422.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10182	
5°	8256	664
15°	1724	524
25°	311	155
35°	77	51
45°	23	19
55°	8	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264830

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10182.1
2.5°	9771.8
5°	8255.7
7.5°	6360.6
10°	4408.6
12.5°	2821.2
15°	1724.1
17.5°	1051.6
20°	672.5
22.5°	450.3
25°	310.6
27.5°	219.4
30°	153.9
32.5°	108.3
35°	76.9
37.5°	54.1
40°	39.9
42.5°	31.3
45°	22.8
47.5°	19.9
50°	14.2
52.5°	11.4
55°	8.5
57.5°	8.5
60°	5.7
62.5°	2.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)