

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B10WFL559030D2WD010 2LBD\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B10WFL559030D2WD010 2LBD\*LI  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 581.4 lumens  
Efficiency: N/A  
Efficacy: 56.4 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559030D2WD010 2LBD\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559030D2WD010 2LBD\*LI

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |  |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0 |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |  |  |  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 87  |    |    |   |  |  |  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |    |    |   |  |  |  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 75  |    |    |   |  |  |  |
| 5   | 92  | 83  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 72  | 77  | 74  | 71  | 69  |    |    |   |  |  |  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  | 74  | 70  | 67  | 73  | 69  | 66  | 65  |    |    |   |  |  |  |
| 7   | 83  | 73  | 67  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 63  | 70  | 66  | 62  | 69  | 65  | 62  | 61  |    |    |   |  |  |  |
| 8   | 79  | 69  | 63  | 59  | 78  | 69  | 63  | 59  | 68  | 62  | 59  | 66  | 62  | 58  | 66  | 61  | 58  | 57  |    |    |   |  |  |  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 53  |    |    |   |  |  |  |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 55  | 52  | 60  | 55  | 52  | 59  | 55  | 52  | 50  |    |    |   |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 299380 |
| 5°  | 287031 |
| 10° | 259199 |
| 15° | 227092 |
| 20° | 193736 |
| 25° | 162493 |
| 30° | 126801 |
| 35° | 87385  |
| 40° | 56127  |
| 45° | 33963  |
| 50° | 19946  |
| 55° | 11143  |
| 60° | 3176   |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559030D2WD010 2LBD\*LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 67.9   | 11.7      |
| 10°-20°   | 157.4  | 27.1      |
| 20°-30°   | 173.0  | 29.7      |
| 30°-40°   | 117.0  | 20.1      |
| 40°-50°   | 50.1   | 8.6       |
| 50°-60°   | 15.3   | 2.6       |
| 60°-70°   | 0.6    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 398.3  | 68.5      |
| 0°-40°    | 515.3  | 88.6      |
| 0°-60°    | 580.8  | 99.9      |
| 0°-90°    | 581.4  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 581.4  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 773 |      |
| 5°  | 738 | 68   |
| 15° | 566 | 157  |
| 25° | 380 | 173  |
| 35° | 185 | 117  |
| 45° | 62  | 50   |
| 55° | 16  | 15   |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559030D2WD010 2LBD\*LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 772.9 |
| 1°    | 768.9 |
| 2°    | 762.3 |
| 3°    | 755.8 |
| 4°    | 747.5 |
| 5°    | 738.2 |
| 6°    | 726.3 |
| 7°    | 712.1 |
| 8°    | 695.0 |
| 9°    | 677.3 |
| 10°   | 659.0 |
| 11°   | 639.5 |
| 12°   | 621.8 |
| 13°   | 603.5 |
| 14°   | 585.2 |
| 15°   | 566.3 |
| 17.5° | 517.3 |
| 20°   | 470.0 |
| 22.5° | 425.2 |
| 25°   | 380.2 |
| 27.5° | 334.2 |
| 30°   | 283.5 |
| 32.5° | 232.0 |
| 35°   | 184.8 |
| 37.5° | 144.7 |
| 40°   | 111.0 |
| 42.5° | 83.8  |
| 45°   | 62.0  |
| 47.5° | 45.4  |
| 50°   | 33.1  |
| 52.5° | 23.6  |
| 55°   | 16.5  |
| 57.5° | 10.7  |
| 60°   | 4.1   |
| 62.5° | 0.6   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559030D2WD010 2LBD\*LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |     |
|-------|-----|
| 85°   | 0.0 |
| 87.5° | 0.0 |



(END OF REPORT)