

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225459

Luminaire Tested: **LD2B15D010 EU2B15FL408050 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408050 2LBDLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1318.1 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225459

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225459

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	105	102	99		107	104	101	98		101	98	96			98	96	94			95
3	105	100	95	92		103	98	94	91		96	92	90			93	91	88			91
4	101	94	90	86		99	93	89	86		91	87	85			89	86	84			88
5	97	90	85	81		95	89	84	81		87	83	80			85	82	79			84
6	93	85	80	77		92	85	80	76		83	79	76			82	78	75			81
7	89	81	76	73		88	81	76	73		80	75	72			79	75	72			78
8	86	78	73	69		85	77	73	69		76	72	69			75	72	69			75
9	83	75	70	66		82	74	69	66		73	69	66			72	69	66			72
10	80	72	67	63		79	71	66	63		70	66	63			70	66	63			69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1146157
5°	1105120
10°	971937
15°	761799
20°	527664
25°	325072
30°	180875
35°	96511
40°	47834
45°	24377
50°	13438
55°	8779
60°	4338
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225459

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.2	19.7
10°-20°	518.9	39.4
20°-30°	354.5	26.9
30°-40°	135.1	10.3
40°-50°	37.5	2.8
50°-60°	11.7	0.9
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1132.6	85.9
0°-40°	1267.7	96.2
0°-60°	1317.0	99.9
0°-90°	1318.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2959	
5°	2842	259
15°	1900	519
25°	761	354
35°	204	135
45°	44	38
55°	13	12
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225459

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2959.0
2.5°	2927.5
5°	2842.2
7.5°	2682.6
10°	2471.1
12.5°	2202.1
15°	1899.7
17.5°	1589.9
20°	1280.1
22.5°	1005.5
25°	760.6
27.5°	558.4
30°	404.4
32.5°	287.6
35°	204.1
37.5°	142.8
40°	94.6
42.5°	63.1
45°	44.5
47.5°	31.5
50°	22.3
52.5°	16.7
55°	13.0
57.5°	9.3
60°	5.6
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)