

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B10WFL559030D2WD010 2LBD\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B10WFL559030D2WD010 2LBD\*GPH  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 564.7 lumens  
Efficiency: N/A  
Efficacy: 54.8 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL559030D2WD010 2LBD\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL559030D2WD010 2LBD\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 113 | 111 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |
| 2   | 108 | 103 | 99  | 95  |  | 105 | 101 | 97  | 94  |  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  | 90  | 88  |
| 3   | 102 | 95  | 90  | 86  |  | 100 | 94  | 89  | 86  |  | 91  | 88  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  |
| 4   | 97  | 89  | 83  | 79  |  | 95  | 88  | 83  | 79  |  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  | 78  | 76  |
| 5   | 92  | 83  | 77  | 73  |  | 90  | 82  | 77  | 72  |  | 80  | 75  | 72  |  | 79  | 74  | 71  |  | 77  | 73  | 70  |
| 6   | 87  | 78  | 72  | 67  |  | 85  | 77  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 66  |  | 73  | 69  | 66  |
| 7   | 83  | 73  | 67  | 63  |  | 81  | 72  | 67  | 62  |  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 61  |
| 8   | 78  | 69  | 63  | 58  |  | 77  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  | 61  | 58  |
| 9   | 75  | 65  | 59  | 55  |  | 73  | 64  | 59  | 55  |  | 63  | 58  | 54  |  | 62  | 58  | 54  |  | 62  | 57  | 54  |
| 10  | 71  | 61  | 55  | 51  |  | 70  | 61  | 55  | 51  |  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  | 54  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 269051 |
| 5°  | 266112 |
| 10° | 245944 |
| 15° | 215383 |
| 20° | 185698 |
| 25° | 158519 |
| 30° | 125414 |
| 35° | 86770  |
| 40° | 56177  |
| 45° | 34073  |
| 50° | 19946  |
| 55° | 11210  |
| 60° | 4261   |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL559030D2WD010 2LBD\*GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 63.4   | 11.2      |
| 10°-20°   | 149.7  | 26.5      |
| 20°-30°   | 168.5  | 29.8      |
| 30°-40°   | 116.2  | 20.6      |
| 40°-50°   | 50.2   | 8.9       |
| 50°-60°   | 15.6   | 2.8       |
| 60°-70°   | 1.0    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 381.7  | 67.6      |
| 0°-40°    | 497.9  | 88.2      |
| 0°-60°    | 563.7  | 99.8      |
| 0°-90°    | 564.7  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 564.7  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 695 |      |
| 5°  | 684 | 63   |
| 15° | 537 | 150  |
| 25° | 371 | 169  |
| 35° | 184 | 116  |
| 45° | 62  | 50   |
| 55° | 17  | 16   |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL559030D2WD010 2LBD\*GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 694.6 |
| 2.5°  | 693.1 |
| 5°    | 684.4 |
| 7.5°  | 661.6 |
| 10°   | 625.3 |
| 12.5° | 582.8 |
| 15°   | 537.1 |
| 17.5° | 491.5 |
| 20°   | 450.5 |
| 22.5° | 411.1 |
| 25°   | 370.9 |
| 27.5° | 328.5 |
| 30°   | 280.4 |
| 32.5° | 230.0 |
| 35°   | 183.5 |
| 37.5° | 144.1 |
| 40°   | 111.1 |
| 42.5° | 83.5  |
| 45°   | 62.2  |
| 47.5° | 45.7  |
| 50°   | 33.1  |
| 52.5° | 23.6  |
| 55°   | 16.6  |
| 57.5° | 11.0  |
| 60°   | 5.5   |
| 62.5° | 1.6   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)