

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225389

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBDC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 606.2 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225389

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225389

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100		108	104	101	99		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	84	81			85
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75		90	83	78	75		81	77	74			80	77	74			79
8	87	80	75	72		86	79	75	71		78	74	71			77	74	71			76
9	84	77	72	69		83	76	72	68		75	71	68			74	71	68			74
10	82	74	69	66		81	73	69	66		73	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	548443
5°	538912
10°	480757
15°	379997
20°	253382
25°	146979
30°	73576
35°	34614
40°	13551
45°	6026
50°	2832
55°	1621
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225389

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.0	21.0
10°-20°	256.5	42.3
20°-30°	161.3	26.6
30°-40°	49.3	8.1
40°-50°	9.7	1.6
50°-60°	2.2	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.9	89.9
0°-40°	594.2	98.0
0°-60°	606.1	100.0
0°-90°	606.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1416	
5°	1386	127
15°	948	256
25°	344	161
35°	73	49
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225389

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1415.9
2.5°	1412.7
5°	1386.0
7.5°	1323.0
10°	1222.3
12.5°	1096.4
15°	947.6
17.5°	782.3
20°	614.7
22.5°	471.4
25°	343.9
27.5°	242.4
30°	164.5
32.5°	111.0
35°	73.2
37.5°	44.8
40°	26.8
42.5°	17.3
45°	11.0
47.5°	7.1
50°	4.7
52.5°	3.2
55°	2.4
57.5°	1.6
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)