

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224401

Luminaire Tested: **LD2B15D010 EU2B15FL408050 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408050 2LBDSQC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1440.2 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224401

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224401

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	87	82	78		93	86	81	78		84	80	77			83	80	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1303923
5°	1280169
10°	1137997
15°	895014
20°	595554
25°	341911
30°	172690
35°	81238
40°	32715
45°	16215
50°	8919
55°	6213
60°	5733
65°	3391
70°	4190
75°	2694
80°	4015
85°	0



TEST NUMBER: P224401

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.5	20.9
10°-20°	604.6	42.0
20°-30°	376.1	26.1
30°-40°	115.6	8.0
40°-50°	25.4	1.8
50°-60°	9.0	0.6
60°-70°	4.6	0.3
70°-80°	2.6	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1282.2	89.0
0°-40°	1397.9	97.1
0°-60°	1432.3	99.4
0°-90°	1440.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1440.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3366	
5°	3292	302
15°	2232	605
25°	800	376
35°	172	116
45°	30	25
55°	9	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224401

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3366.3
2.5°	3351.5
5°	3292.4
7.5°	3142.7
10°	2893.3
12.5°	2594.0
15°	2231.9
17.5°	1836.5
20°	1444.8
22.5°	1095.6
25°	800.0
27.5°	563.5
30°	386.1
32.5°	260.5
35°	171.8
37.5°	103.5
40°	64.7
42.5°	44.3
45°	29.6
47.5°	20.3
50°	14.8
52.5°	12.9
55°	9.2
57.5°	7.4
60°	7.4
62.5°	5.5
65°	3.7
67.5°	3.7
70°	3.7
72.5°	3.7
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)