

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224969

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 576.5 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224969

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224969

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96						
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91						
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87						
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83						
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79						
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76						
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73						
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70						
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67						
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	553053
5°	531486
10°	462664
15°	361270
20°	240233
25°	137577
30°	68387
35°	31445
40°	12591
45°	5752
50°	2651
55°	1486
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224969

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.4	21.6
10°-20°	244.3	42.4
20°-30°	151.2	26.2
30°-40°	45.3	7.9
40°-50°	9.1	1.6
50°-60°	2.2	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.9	90.2
0°-40°	565.1	98.0
0°-60°	576.4	100.0
0°-90°	576.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1428	
5°	1367	124
15°	901	244
25°	322	151
35°	66	45
45°	10	9
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224969

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1427.8
1°	1420.1
2°	1412.9
3°	1398.5
4°	1385.1
5°	1366.9
6°	1341.9
7°	1310.3
8°	1269.9
9°	1223.9
10°	1176.3
11°	1127.0
12°	1074.3
13°	1019.5
14°	960.7
15°	900.9
17.5°	743.0
20°	582.8
22.5°	441.1
25°	321.9
27.5°	226.0
30°	152.9
32.5°	100.9
35°	66.5
37.5°	41.6
40°	24.9
42.5°	16.1
45°	10.5
47.5°	6.7
50°	4.4
52.5°	3.3
55°	2.2
57.5°	1.6
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224969

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)