

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224248

Luminaire Tested: **LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1271.5 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224248

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224248

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			85
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			82
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			79
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			76
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			74
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1157390
5°	1135176
10°	1008358
15°	795764
20°	530755
25°	305498
30°	154755
35°	72537
40°	29681
45°	13421
50°	6870
55°	4390
60°	2556
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224248

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.2	21.0
10°-20°	536.2	42.2
20°-30°	335.9	26.4
30°-40°	103.9	8.2
40°-50°	21.5	1.7
50°-60°	6.0	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1139.3	89.6
0°-40°	1243.3	97.8
0°-60°	1270.7	99.9
0°-90°	1271.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1271.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2988	
5°	2920	267
15°	1984	536
25°	715	336
35°	153	104
45°	24	21
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224248

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2988.0
2.5°	2973.3
5°	2919.5
7.5°	2782.4
10°	2563.7
12.5°	2294.5
15°	1984.4
17.5°	1627.0
20°	1287.6
22.5°	979.1
25°	714.8
27.5°	502.6
30°	346.0
32.5°	231.7
35°	153.4
37.5°	96.3
40°	58.7
42.5°	37.5
45°	24.5
47.5°	16.3
50°	11.4
52.5°	8.2
55°	6.5
57.5°	4.9
60°	3.3
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)