

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224765

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 571.6 lumens
Efficiency: N/A
Efficacy: 55.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224765

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224765

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517456
5°	508040
10°	451612
15°	355215
20°	236358
25°	135696
30°	68522
35°	32249
40°	12995
45°	6464
50°	3495
55°	2499
60°	2324
65°	1375
70°	1699
75°	1048
80°	1561
85°	0



TEST NUMBER: P224765

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	20.9
10°-20°	239.9	42.0
20°-30°	149.3	26.1
30°-40°	45.9	8.0
40°-50°	10.1	1.8
50°-60°	3.6	0.6
60°-70°	1.8	0.3
70°-80°	1.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.9	89.0
0°-40°	554.8	97.0
0°-60°	568.5	99.4
0°-90°	571.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	571.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1336	
5°	1307	120
15°	886	240
25°	318	149
35°	68	46
45°	12	10
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224765

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1335.9
2.5°	1330.1
5°	1306.6
7.5°	1247.2
10°	1148.2
12.5°	1029.5
15°	885.8
17.5°	728.8
20°	573.4
22.5°	434.8
25°	317.5
27.5°	223.6
30°	153.2
32.5°	103.4
35°	68.2
37.5°	41.1
40°	25.7
42.5°	17.6
45°	11.8
47.5°	8.1
50°	5.8
52.5°	5.1
55°	3.7
57.5°	3.0
60°	3.0
62.5°	2.2
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)