

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224660

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 566.6 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224660

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224660

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	512962
5°	503607
10°	447718
15°	352127
20°	234297
25°	134542
30°	67940
35°	31965
40°	12894
45°	6354
50°	3495
55°	2431
60°	2247
65°	1375
70°	1699
75°	1048
80°	1561
85°	0



TEST NUMBER: P224660

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.6	20.9
10°-20°	237.8	42.0
20°-30°	148.0	26.1
30°-40°	45.5	8.0
40°-50°	10.0	1.8
50°-60°	3.5	0.6
60°-70°	1.8	0.3
70°-80°	1.1	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.4	89.0
0°-40°	549.9	97.1
0°-60°	563.5	99.4
0°-90°	566.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1324	
5°	1295	119
15°	878	238
25°	315	148
35°	68	45
45°	12	10
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224660

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1324.3
2.5°	1318.6
5°	1295.2
7.5°	1236.4
10°	1138.3
12.5°	1020.5
15°	878.1
17.5°	722.5
20°	568.4
22.5°	431.0
25°	314.8
27.5°	221.7
30°	151.9
32.5°	102.5
35°	67.6
37.5°	40.7
40°	25.5
42.5°	17.5
45°	11.6
47.5°	8.0
50°	5.8
52.5°	5.1
55°	3.6
57.5°	2.9
60°	2.9
62.5°	2.1
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)