

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15WFL558050 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15WFL558050 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1259.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	102	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	96	89	83	79	95	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68
8	78	68	62	58	77	68	62	58	67	61	57		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	60	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	590586
5°	579117
10°	538339
15°	476600
20°	412617
25°	346869
30°	271626
35°	194063
40°	129597
45°	80361
50°	48148
55°	28836
60°	12937
65°	1741
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	11.0
10°-20°	331.0	26.3
20°-30°	369.2	29.3
30°-40°	258.6	20.5
40°-50°	118.1	9.4
50°-60°	39.5	3.1
60°-70°	4.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.5	66.6
0°-40°	1097.1	87.1
0°-60°	1254.6	99.7
0°-90°	1259.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1259.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1525	
5°	1489	138
15°	1188	331
25°	812	369
35°	410	259
45°	147	118
55°	43	39
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1524.7
2.5°	1517.3
5°	1489.4
7.5°	1437.4
10°	1368.7
12.5°	1281.4
15°	1188.5
17.5°	1092.0
20°	1001.0
22.5°	910.0
25°	811.6
27.5°	711.3
30°	607.3
32.5°	505.1
35°	410.4
37.5°	326.9
40°	256.3
42.5°	195.0
45°	146.7
47.5°	109.6
50°	79.9
52.5°	57.6
55°	42.7
57.5°	29.7
60°	16.7
62.5°	5.6
65°	1.9
67.5°	1.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)