

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265134

Luminaire Tested: **LD2B15D010 EU2B1510SP159050 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159050 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1140.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265134

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P265134

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	91		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	88	85		90	87	85		89	86	84		88	86	84
8	95	89	86	83		94	89	85	83		88	85	82		87	84	82		86	84	82
9	93	87	83	81		92	87	83	81		86	83	81		85	82	80		85	82	80
10	91	85	82	79		91	85	81	79		84	81	79		84	81	79		83	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4024451
5°	3275510
10°	1769335
15°	705470
20°	282883
25°	135438
30°	70242
35°	37101
40°	20609
45°	12768
50°	8750
55°	5849
60°	4539
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265134

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	531.9	46.7
10°-20°	419.7	36.8
20°-30°	123.8	10.9
30°-40°	41.2	3.6
40°-50°	15.5	1.4
50°-60°	6.8	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.3	94.3
0°-40°	1116.6	97.9
0°-60°	1138.9	99.9
0°-90°	1140.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1140.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8157	
5°	6614	532
15°	1381	420
25°	249	124
35°	62	41
45°	18	15
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265134

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8157.2
2.5°	7828.4
5°	6613.9
7.5°	5095.7
10°	3531.8
12.5°	2260.2
15°	1381.2
17.5°	842.4
20°	538.8
22.5°	360.7
25°	248.8
27.5°	175.8
30°	123.3
32.5°	86.8
35°	61.6
37.5°	43.4
40°	32.0
42.5°	25.1
45°	18.3
47.5°	16.0
50°	11.4
52.5°	9.1
55°	6.8
57.5°	6.8
60°	4.6
62.5°	2.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)