

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225457

Luminaire Tested: **LSRWM2B15FL408035D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL408035D010 2LBDLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1275.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225457

CATALOG NUMBER: LSRWM2B15FL408035D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225457

CATALOG NUMBER: LSRWM2B15FL408035D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91
4	101	94	90	86	99	93	89	86	91	87	85		89	86	84		88
5	97	90	85	81	95	89	84	81	87	83	80		85	82	79		84
6	93	85	80	77	92	85	80	76	83	79	76		82	78	75		81
7	89	81	76	73	88	81	76	73	80	75	72		79	75	72		78
8	86	78	73	69	85	77	73	69	76	72	69		75	72	69		75
9	83	75	70	66	82	74	69	66	73	69	66		72	69	66		72
10	80	72	67	63	79	71	66	63	70	66	63		70	66	63		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1108700
5°	1068959
10°	940156
15°	736896
20°	510392
25°	314473
30°	174971
35°	93343
40°	46266
45°	23610
50°	12956
55°	8509
60°	4183
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225457

CATALOG NUMBER: LSRWM2B15FL408035D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.7	19.7
10°-20°	501.9	39.4
20°-30°	342.9	26.9
30°-40°	130.7	10.3
40°-50°	36.3	2.8
50°-60°	11.4	0.9
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1095.6	85.9
0°-40°	1226.3	96.2
0°-60°	1273.9	99.9
0°-90°	1275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2862	
5°	2749	251
15°	1838	502
25°	736	343
35°	197	131
45°	43	36
55°	13	11
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225457

CATALOG NUMBER: LSRWM2B15FL408035D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2862.3
2.5°	2831.8
5°	2749.2
7.5°	2594.9
10°	2390.3
12.5°	2130.1
15°	1837.6
17.5°	1537.9
20°	1238.2
22.5°	972.6
25°	735.8
27.5°	540.2
30°	391.2
32.5°	278.2
35°	197.4
37.5°	138.2
40°	91.5
42.5°	61.0
45°	43.1
47.5°	30.5
50°	21.5
52.5°	16.2
55°	12.6
57.5°	9.0
60°	5.4
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)