

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265144

Luminaire Tested: **LD2B15D010 EU2B1510SP159050 2LBSQLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159050 2LBSQLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1089.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265144

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBSQLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P265144

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBSQLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	88	85	90	87	85		89	86	84		88
8	95	89	86	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	87	83	81	86	83	81		85	82	80		85
10	91	85	82	79	91	85	81	79	84	81	79		84	81	79		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3844374
5°	3128966
10°	1690182
15°	673904
20°	270230
25°	129395
30°	67109
35°	35475
40°	19643
45°	12140
50°	8366
55°	5591
60°	4342
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265144

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBSQLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.1	46.7
10°-20°	400.9	36.8
20°-30°	118.3	10.9
30°-40°	39.4	3.6
40°-50°	14.8	1.4
50°-60°	6.5	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1027.2	94.3
0°-40°	1066.6	97.9
0°-60°	1087.9	99.9
0°-90°	1089.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7792	
5°	6318	508
15°	1319	401
25°	238	118
35°	59	39
45°	17	15
55°	6	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265144

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBSQLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7792.2
2.5°	7478.2
5°	6318.0
7.5°	4867.7
10°	3373.8
12.5°	2159.1
15°	1319.4
17.5°	804.7
20°	514.7
22.5°	344.6
25°	237.7
27.5°	167.9
30°	117.8
32.5°	82.9
35°	58.9
37.5°	41.4
40°	30.5
42.5°	24.0
45°	17.4
47.5°	15.3
50°	10.9
52.5°	8.7
55°	6.5
57.5°	6.5
60°	4.4
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)