

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225147

Luminaire Tested: **LSR2B15FL409035D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409035D010 2LBD*GPH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1165.5 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225147

CATALOG NUMBER: LSR2B15FL409035D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225147

CATALOG NUMBER: LSR2B15FL409035D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	100		108	104	101	98		101	99	96		98	96	94		95	94	92
3	106	100	96	93		104	99	95	92		96	93	91		94	92	89		92	90	88
4	102	95	91	87		100	94	90	87		92	89	86		90	87	85		89	86	84
5	98	91	86	83		96	90	85	82		88	84	81		87	83	81		85	82	80
6	94	87	82	78		93	86	81	78		85	81	78		83	80	77		82	79	77
7	91	83	78	75		89	82	78	74		81	77	74		80	76	74		79	76	73
8	87	80	75	71		86	79	74	71		78	74	71		77	73	71		76	73	70
9	84	76	72	68		83	76	71	68		75	71	68		74	70	68		73	70	68
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1057300
5°	1035909
10°	920490
15°	722179
20°	485701
25°	282590
30°	141561
35°	66059
40°	30794
45°	13037
50°	6267
55°	3984
60°	2324
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225147

CATALOG NUMBER: LSR2B15FL409035D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.9	20.9
10°-20°	488.8	41.9
20°-30°	309.1	26.5
30°-40°	96.2	8.3
40°-50°	21.4	1.8
50°-60°	5.4	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1041.8	89.4
0°-40°	1138.0	97.6
0°-60°	1164.8	99.9
0°-90°	1165.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1165.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2730	
5°	2664	244
15°	1801	489
25°	661	309
35°	140	96
45°	24	21
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225147

CATALOG NUMBER: LSR2B15FL409035D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2729.6
2.5°	2717.7
5°	2664.2
7.5°	2537.9
10°	2340.3
12.5°	2090.7
15°	1800.9
17.5°	1487.4
20°	1178.3
22.5°	900.5
25°	661.2
27.5°	463.6
30°	316.5
32.5°	209.5
35°	139.7
37.5°	93.6
40°	60.9
42.5°	37.1
45°	23.8
47.5°	16.3
50°	10.4
52.5°	7.4
55°	5.9
57.5°	4.5
60°	3.0
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)