

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224352

Luminaire Tested: **LD2B15D010 EU2B15FL409050 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409050 2LBDSQC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1152.4 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224352

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224352

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			85
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			82
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			79
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			76
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			74
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1048972
5°	1028833
10°	913882
15°	721217
20°	481002
25°	276863
30°	140263
35°	65728
40°	26900
45°	12161
50°	6267
55°	3984
60°	2324
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224352

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.2	21.0
10°-20°	486.0	42.2
20°-30°	304.4	26.4
30°-40°	94.2	8.2
40°-50°	19.5	1.7
50°-60°	5.4	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1032.6	89.6
0°-40°	1126.8	97.8
0°-60°	1151.7	99.9
0°-90°	1152.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2708	
5°	2646	242
15°	1798	486
25°	648	304
35°	139	94
45°	22	19
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224352

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2708.1
2.5°	2694.8
5°	2646.0
7.5°	2521.7
10°	2323.5
12.5°	2079.5
15°	1798.5
17.5°	1474.6
20°	1166.9
22.5°	887.4
25°	647.8
27.5°	455.5
30°	313.6
32.5°	210.0
35°	139.0
37.5°	87.3
40°	53.2
42.5°	34.0
45°	22.2
47.5°	14.8
50°	10.4
52.5°	7.4
55°	5.9
57.5°	4.4
60°	3.0
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)