

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B15WFL559035D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15WFL559035D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1099.1 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL559035D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL559035D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			93
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			86
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			80
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			74
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			69
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			64
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			60
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			56
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	515558
5°	512278
10°	476273
15°	418093
20°	360391
25°	308190
30°	244566
35°	170514
40°	107854
45°	65844
50°	38928
55°	21272
60°	4648
65°	4124
70°	3398
75°	4490
80°	3346
85°	6666



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL559035D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	11.1
10°-20°	290.4	26.4
20°-30°	327.6	29.8
30°-40°	226.6	20.6
40°-50°	96.6	8.8
50°-60°	27.9	2.5
60°-70°	4.1	0.4
70°-80°	2.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.2	67.4
0°-40°	966.9	88.0
0°-60°	1091.4	99.3
0°-90°	1099.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1099.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1331	
5°	1318	122
15°	1043	290
25°	721	328
35°	361	227
45°	120	97
55°	32	28
65°	4	4
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL559035D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1331.0
2.5°	1329.5
5°	1317.5
7.5°	1277.0
10°	1210.9
12.5°	1129.7
15°	1042.6
17.5°	952.5
20°	874.3
22.5°	800.7
25°	721.1
27.5°	637.0
30°	546.8
32.5°	449.2
35°	360.6
37.5°	279.4
40°	213.3
42.5°	160.7
45°	120.2
47.5°	87.1
50°	64.6
52.5°	46.6
55°	31.5
57.5°	13.5
60°	6.0
62.5°	4.5
65°	4.5
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)