

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225489

Luminaire Tested: **LSSQWM2B15FL409035D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409035D010 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1081.1 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225489

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P225489

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88
5	97	90	85	81	96	89	84	81	87	83	80		86	82	80		84
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75
9	83	75	70	67	82	75	70	67	74	69	66		73	69	66		72
10	80	72	67	64	79	72	67	64	71	67	64		70	66	64		70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	950315
5°	918678
10°	810596
15°	638609
20°	438833
25°	265024
30°	143663
35°	73814
40°	36103
45°	17091
50°	8979
55°	6010
60°	3486
65°	1375
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225489

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.9	20.0
10°-20°	433.5	40.1
20°-30°	289.6	26.8
30°-40°	104.9	9.7
40°-50°	27.1	2.5
50°-60°	8.1	0.7
60°-70°	2.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	939.0	86.9
0°-40°	1043.9	96.6
0°-60°	1079.1	99.8
0°-90°	1081.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1081.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2453	
5°	2363	216
15°	1592	434
25°	620	290
35°	156	105
45°	31	27
55°	9	8
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225489

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2453.4
2.5°	2431.1
5°	2362.7
7.5°	2237.8
10°	2060.9
12.5°	1843.8
15°	1592.5
17.5°	1324.9
20°	1064.6
22.5°	825.3
25°	620.1
27.5°	452.0
30°	321.2
32.5°	226.0
35°	156.1
37.5°	108.5
40°	71.4
42.5°	46.1
45°	31.2
47.5°	22.3
50°	14.9
52.5°	11.9
55°	8.9
57.5°	5.9
60°	4.5
62.5°	3.0
65°	1.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)