

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224671

Luminaire Tested: **LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 762.7 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224671

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224671

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	87	82	78		93	86	81	78		84	80	77		83	80	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	690483
5°	677917
10°	602647
15°	473954
20°	315378
25°	181042
30°	91466
35°	43030
40°	17344
45°	8600
50°	4700
55°	3309
60°	3021
65°	1741
70°	2152
75°	1497
80°	2231
85°	0



TEST NUMBER: P224671

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	20.9
10°-20°	320.2	42.0
20°-30°	199.2	26.1
30°-40°	61.2	8.0
40°-50°	13.5	1.8
50°-60°	4.8	0.6
60°-70°	2.4	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	679.0	89.0
0°-40°	740.2	97.1
0°-60°	758.5	99.4
0°-90°	762.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1783	
5°	1744	160
15°	1182	320
25°	424	199
35°	91	61
45°	16	13
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224671

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1782.6
2.5°	1774.8
5°	1743.5
7.5°	1664.2
10°	1532.2
12.5°	1373.7
15°	1181.9
17.5°	972.6
20°	765.1
22.5°	580.2
25°	423.6
27.5°	298.4
30°	204.5
32.5°	137.9
35°	91.0
37.5°	54.8
40°	34.3
42.5°	23.5
45°	15.7
47.5°	10.7
50°	7.8
52.5°	6.9
55°	4.9
57.5°	3.9
60°	3.9
62.5°	3.0
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)