

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264216

Luminaire Tested: **LD2B20D010 EU2B2010SP159024 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159024 2LBD*WMH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1198.0 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264216

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P264216

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	102		101	100	100
2	113	109	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	96	95
4	107	103	99	97		106	102	99	96		100	97	95		98	96	94		96	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	91
6	103	98	94	92		102	97	94	91		96	93	91		95	92	90		93	91	90
7	101	95	92	90		100	95	92	89		94	91	89		93	90	89		92	90	88
8	99	93	90	88		98	93	90	88		92	89	87		91	89	87		91	88	87
9	97	92	88	86		96	91	88	86		91	88	86		90	87	86		89	87	85
10	95	90	87	85		95	90	87	85		89	86	85		89	86	84		88	86	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5652890
5°	4531058
10°	1977640
15°	612868
20°	213633
25°	94338
30°	42726
35°	22224
40°	12688
45°	6000
50°	3761
55°	2150
60°	1184
65°	1401
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264216

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	694.8	58.0
10°-20°	380.5	31.8
20°-30°	86.7	7.2
30°-40°	24.9	2.1
40°-50°	7.7	0.6
50°-60°	2.3	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1162.0	97.0
0°-40°	1186.9	99.1
0°-60°	1196.9	99.9
0°-90°	1198.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1198.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11458	
5°	9149	695
15°	1200	380
25°	173	87
35°	37	25
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264216

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11457.9
1°	11315.3
2°	11019.0
3°	10559.2
4°	9927.3
5°	9149.1
6°	8195.1
7°	7129.2
8°	6016.6
9°	4939.7
10°	3947.6
11°	3107.9
12°	2446.5
13°	1925.2
14°	1520.8
15°	1199.9
16°	946.6
17°	753.6
18°	606.1
19°	493.0
20°	406.9
22.5°	263.1
25°	173.3
26°	146.3
27°	124.2
28°	104.5
29°	87.3
30°	75.0
32.5°	51.6
35°	36.9
37.5°	27.0
40°	19.7
42.5°	13.5
45°	8.6
47.5°	6.1
50°	4.9
52.5°	3.7
55°	2.5
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2



TEST NUMBER: P264216

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBD*WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)