

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B05WFL559024D010 2LBDL*WH**

Issue Date: 3/3/2020


Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05WFL559024D010 2LBDL*WH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 477.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B05WFL559024D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559024D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 |
| 2 | 108 | 103 | 99 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 |
| 3 | 102 | 96 | 90 | 86 | 100 | 94 | 90 | 86 | 92 | 88 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 83 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 80 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 71 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 64 |
| 7 | 83 | 73 | 67 | 63 | 81 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 60 |
| 8 | 79 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 56 |
| 9 | 75 | 65 | 59 | 55 | 74 | 64 | 59 | 55 | 64 | 58 | 55 | 63 | 58 | 54 | 62 | 57 | 54 | 53 |
| 10 | 71 | 61 | 56 | 52 | 70 | 61 | 55 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 59 | 54 | 51 | 50 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 238760 |
| 5° | 230535 |
| 10° | 208696 |
| 15° | 182820 |
| 20° | 157421 |
| 25° | 133815 |
| 30° | 105198 |
| 35° | 73104 |
| 40° | 47379 |
| 45° | 28376 |
| 50° | 16572 |
| 55° | 9319 |
| 60° | 3564 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559024D010 2LBDL*WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 54.6 | 11.4 |
| 10°-20° | 126.9 | 26.6 |
| 20°-30° | 142.2 | 29.8 |
| 30°-40° | 97.8 | 20.5 |
| 40°-50° | 42.0 | 8.8 |
| 50°-60° | 12.8 | 2.7 |
| 60°-70° | 0.7 | 0.2 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 323.7 | 67.9 |
| 0°-40° | 421.5 | 88.4 |
| 0°-60° | 476.3 | 99.8 |
| 0°-90° | 477.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 477.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 616 | |
| 5° | 593 | 55 |
| 15° | 456 | 127 |
| 25° | 313 | 142 |
| 35° | 155 | 98 |
| 45° | 52 | 42 |
| 55° | 14 | 13 |
| 65° | 0 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559024D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 616.4 |
| 2.5° | 609.9 |
| 5° | 592.9 |
| 7.5° | 565.3 |
| 10° | 530.6 |
| 12.5° | 493.9 |
| 15° | 455.9 |
| 17.5° | 416.0 |
| 20° | 381.9 |
| 22.5° | 347.9 |
| 25° | 313.1 |
| 27.5° | 276.5 |
| 30° | 235.2 |
| 32.5° | 193.3 |
| 35° | 154.6 |
| 37.5° | 121.2 |
| 40° | 93.7 |
| 42.5° | 70.1 |
| 45° | 51.8 |
| 47.5° | 38.0 |
| 50° | 27.5 |
| 52.5° | 19.0 |
| 55° | 13.8 |
| 57.5° | 9.2 |
| 60° | 4.6 |
| 62.5° | 0.7 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)