

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B05WFL559024D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05WFL559024D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 518.9 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559024D010 2LBDC*MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559024D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93						
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86						
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80						
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74						
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69						
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64						
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60						
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56						
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53						
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243447
5°	241888
10°	224901
15°	197417
20°	170199
25°	145526
30°	115485
35°	80528
40°	50918
45°	31114
50°	18379
55°	10062
60°	2169
65°	1925
70°	1586
75°	2095
80°	1561
85°	3111



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559024D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	11.1
10°-20°	137.1	26.4
20°-30°	154.7	29.8
30°-40°	107.0	20.6
40°-50°	45.6	8.8
50°-60°	13.2	2.5
60°-70°	1.9	0.4
70°-80°	1.2	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.6	67.4
0°-40°	456.6	88.0
0°-60°	515.4	99.3
0°-90°	518.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	628	
5°	622	58
15°	492	137
25°	340	155
35°	170	107
45°	57	46
55°	15	13
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559024D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	628.5
2.5°	627.8
5°	622.1
7.5°	603.0
10°	571.8
12.5°	533.5
15°	492.3
17.5°	449.8
20°	412.9
22.5°	378.1
25°	340.5
27.5°	300.8
30°	258.2
32.5°	212.1
35°	170.3
37.5°	131.9
40°	100.7
42.5°	75.9
45°	56.8
47.5°	41.1
50°	30.5
52.5°	22.0
55°	14.9
57.5°	6.4
60°	2.8
62.5°	2.1
65°	2.1
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)