

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224439

Luminaire Tested: **LSSQWM2B05FL409024D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409024D010 2LBDL*WH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 529.3 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224439

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224439

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		82
7	90	83	78	75	89	82	78	74	81	77	74		80	76	74		79
8	87	79	75	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	488327
5°	469857
10°	413577
15°	324858
20°	220859
25°	128986
30°	65704
35°	31067
40°	13551
45°	5861
50°	2832
55°	1823
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224439

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	20.9
10°-20°	220.3	41.6
20°-30°	141.4	26.7
30°-40°	44.9	8.5
40°-50°	9.6	1.8
50°-60°	2.5	0.5
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	472.1	89.2
0°-40°	516.9	97.7
0°-60°	529.0	99.9
0°-90°	529.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	529.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1261	
5°	1208	110
15°	810	220
25°	302	141
35°	66	45
45°	11	10
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224439

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1260.7
2.5°	1248.7
5°	1208.4
7.5°	1142.7
10°	1051.5
12.5°	940.2
15°	810.1
17.5°	671.3
20°	535.8
22.5°	409.1
25°	301.8
27.5°	215.3
30°	146.9
32.5°	98.6
35°	65.7
37.5°	43.6
40°	26.8
42.5°	16.8
45°	10.7
47.5°	7.4
50°	4.7
52.5°	3.4
55°	2.7
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)