

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224647

Luminaire Tested: **LSSQWM2B05FL409024D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409024D010 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 510.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224647

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224647

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			88
5	97	91	86	82		96	90	85	82		88	84	81			86	83	80			85
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			82
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461716
5°	453293
10°	402958
15°	316918
20°	210884
25°	121079
30°	61142
35°	28750
40°	11579
45°	5752
50°	3134
55°	2229
60°	2014
65°	1192
70°	1472
75°	1048
80°	1561
85°	0



TEST NUMBER: P224647

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.8	20.9
10°-20°	214.1	42.0
20°-30°	133.2	26.1
30°-40°	40.9	8.0
40°-50°	9.0	1.8
50°-60°	3.2	0.6
60°-70°	1.6	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.0	89.0
0°-40°	494.9	97.0
0°-60°	507.1	99.4
0°-90°	510.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	510.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1192	
5°	1166	107
15°	790	214
25°	283	133
35°	61	41
45°	10	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224647

CATALOG NUMBER: LSSQWM2B05FL409024D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1192.0
2.5°	1186.7
5°	1165.8
7.5°	1112.8
10°	1024.5
12.5°	918.5
15°	790.3
17.5°	650.3
20°	511.6
22.5°	387.9
25°	283.3
27.5°	199.5
30°	136.7
32.5°	92.2
35°	60.8
37.5°	36.6
40°	22.9
42.5°	15.7
45°	10.5
47.5°	7.2
50°	5.2
52.5°	4.6
55°	3.3
57.5°	2.6
60°	2.6
62.5°	2.0
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)