

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222977

Luminaire Tested: **LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1160.4 lumens
Efficiency: N/A
Efficacy: 55.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222977

CATALOG NUMBER: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P222977

CATALOG NUMBER: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	105	101	99		107	103	100	98		101	98	96		99	97	95		96	95	93
4	106	101	97	95		104	100	97	94		98	95	93		96	94	92		95	93	91
5	103	98	94	91		102	97	94	91		95	92	90		94	91	89		93	90	89
6	101	95	91	89		99	94	91	88		93	90	88		92	89	87		91	88	87
7	98	92	89	86		97	92	88	86		91	88	85		90	87	85		89	87	85
8	96	90	86	84		95	90	86	84		89	86	83		88	85	83		87	85	83
9	94	88	84	82		93	88	84	82		87	84	82		86	83	81		85	83	81
10	92	86	82	80		91	86	82	80		85	82	80		84	82	80		84	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2666567
5°	2462121
10°	1666542
15°	566988
20°	208246
25°	110395
30°	56758
35°	26480
40°	8647
45°	4382
50°	2049
55°	743
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222977

CATALOG NUMBER: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	538.6	46.4
10°-20°	452.9	39.0
20°-30°	124.3	10.7
30°-40°	36.2	3.1
40°-50°	6.7	0.6
50°-60°	1.5	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1115.8	96.2
0°-40°	1152.0	99.3
0°-60°	1160.2	100.0
0°-90°	1160.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6884	
5°	6332	539
15°	1414	453
25°	258	124
35°	56	36
45°	8	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222977

CATALOG NUMBER: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	6884.2
1°	6844.2
2°	6773.3
3°	6671.6
4°	6532.2
5°	6332.2
6°	6059.0
7°	5717.2
8°	5300.0
9°	4807.4
10°	4237.1
11°	3611.8
12°	2961.5
13°	2340.8
14°	1811.6
15°	1413.9
17.5°	797.8
20°	505.2
22.5°	360.0
25°	258.3
27.5°	182.9
30°	126.9
32.5°	89.2
35°	56.0
37.5°	22.9
40°	17.1
42.5°	12.6
45°	8.0
47.5°	4.6
50°	3.4
52.5°	2.3
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222977

CATALOG NUMBER: LD2B20D010 EU2B20NFL259024 2LBDSQLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)