

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL558027D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL558027D010 2LBD*GPH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 696.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558027D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558027D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	72		80	75	72		79	74	71		77	73	70
6	87	78	72	67		85	77	71	67		75	70	67		74	70	66		73	69	66
7	83	73	67	63		81	72	67	62		71	66	62		70	65	62		69	65	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	58
9	75	65	59	55		73	64	59	55		63	58	54		62	58	54		62	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	331607
5°	327974
10°	303133
15°	265469
20°	228856
25°	195402
30°	154576
35°	106961
40°	69223
45°	42015
50°	24586
55°	13776
60°	5268
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558027D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	11.2
10°-20°	184.6	26.5
20°-30°	207.7	29.8
30°-40°	143.2	20.6
40°-50°	61.9	8.9
50°-60°	19.2	2.8
60°-70°	1.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.4	67.6
0°-40°	613.7	88.2
0°-60°	694.7	99.8
0°-90°	696.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	844	78
15°	662	185
25°	457	208
35°	226	143
45°	77	62
55°	20	19
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558027D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	856.1
2.5°	854.2
5°	843.5
7.5°	815.4
10°	770.7
12.5°	718.3
15°	662.0
17.5°	605.7
20°	555.2
22.5°	506.7
25°	457.2
27.5°	404.8
30°	345.6
32.5°	283.4
35°	226.2
37.5°	177.6
40°	136.9
42.5°	102.9
45°	76.7
47.5°	56.3
50°	40.8
52.5°	29.1
55°	20.4
57.5°	13.6
60°	6.8
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)