

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225342

Luminaire Tested: **LSRWM2B05FL409027D010 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225342  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B05FL409027D010 2LBDC\*MW  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 518.0 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225342

CATALOG NUMBER: LSRWM2B05FL409027D010 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P225342

CATALOG NUMBER: LSRWM2B05FL409027D010 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 110 | 106 | 102 | 99  |  | 108 | 104 | 101 | 98  |  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 94  | 92  |
| 3   | 105 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 92  | 90  | 88  |
| 4   | 101 | 95  | 90  | 87  |  | 100 | 94  | 90  | 86  |  | 92  | 88  | 85  |  | 90  | 87  | 85  |  | 88  | 86  | 84  |
| 5   | 98  | 91  | 86  | 82  |  | 96  | 90  | 85  | 82  |  | 88  | 84  | 81  |  | 86  | 83  | 80  |  | 85  | 82  | 80  |
| 6   | 94  | 86  | 82  | 78  |  | 93  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  | 79  | 76  |
| 7   | 90  | 83  | 78  | 74  |  | 89  | 82  | 77  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 73  |  | 79  | 76  | 73  |
| 8   | 87  | 79  | 74  | 71  |  | 86  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 9   | 84  | 76  | 71  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  | 70  | 67  |
| 10  | 81  | 73  | 68  | 65  |  | 80  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  |  | 71  | 67  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 468960 |
| 5°  | 460408 |
| 10° | 409290 |
| 15° | 321891 |
| 20° | 214182 |
| 25° | 122960 |
| 30° | 62126  |
| 35° | 29223  |
| 40° | 11782  |
| 45° | 5807   |
| 50° | 3194   |
| 55° | 2229   |
| 60° | 2092   |
| 65° | 1192   |
| 70° | 1472   |
| 75° | 1048   |
| 80° | 1561   |
| 85° | 0      |



TEST NUMBER: P225342

CATALOG NUMBER: LSRWM2B05FL409027D010 2LBDC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 108.4  | 20.9      |
| 10°-20°   | 217.4  | 42.0      |
| 20°-30°   | 135.3  | 26.1      |
| 30°-40°   | 41.6   | 8.0       |
| 40°-50°   | 9.1    | 1.8       |
| 50°-60°   | 3.3    | 0.6       |
| 60°-70°   | 1.6    | 0.3       |
| 70°-80°   | 1.0    | 0.2       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 461.1  | 89.0      |
| 0°-40°    | 502.7  | 97.0      |
| 0°-60°    | 515.1  | 99.4      |
| 0°-90°    | 518.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 518.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1211 |      |
| 5°  | 1184 | 108  |
| 15° | 803  | 217  |
| 25° | 288  | 135  |
| 35° | 62   | 42   |
| 45° | 11   | 9    |
| 55° | 3    | 3    |
| 65° | 1    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P225342

CATALOG NUMBER: LSRWM2B05FL409027D010 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1210.7 |
| 2.5°  | 1205.4 |
| 5°    | 1184.1 |
| 7.5°  | 1130.3 |
| 10°   | 1040.6 |
| 12.5° | 932.9  |
| 15°   | 802.7  |
| 17.5° | 660.5  |
| 20°   | 519.6  |
| 22.5° | 394.0  |
| 25°   | 287.7  |
| 27.5° | 202.7  |
| 30°   | 138.9  |
| 32.5° | 93.7   |
| 35°   | 61.8   |
| 37.5° | 37.2   |
| 40°   | 23.3   |
| 42.5° | 15.9   |
| 45°   | 10.6   |
| 47.5° | 7.3    |
| 50°   | 5.3    |
| 52.5° | 4.7    |
| 55°   | 3.3    |
| 57.5° | 2.7    |
| 60°   | 2.7    |
| 62.5° | 2.0    |
| 65°   | 1.3    |
| 67.5° | 1.3    |
| 70°   | 1.3    |
| 72.5° | 1.3    |
| 75°   | 0.7    |
| 77.5° | 0.7    |
| 80°   | 0.7    |
| 82.5° | 0.7    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)