

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264948

Luminaire Tested: **LD2B20D010 EU2B2010SP159027 2LBLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159027 2LBLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1301.0 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264948

CATALOG NUMBER: LD2B20D010 EU2B2010SP159027 2LBC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264948

CATALOG NUMBER: LD2B20D010 EU2B2010SP159027 2LBLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	106	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	91		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	88	85		90	87	85		89	86	84		88	86	84
8	95	89	86	83		94	89	85	83		88	85	82		87	84	82		86	84	82
9	93	87	83	81		92	87	83	81		86	83	81		85	82	80		85	82	80
10	91	85	82	79		91	85	81	79		84	81	79		84	81	79		83	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4592804
5°	3738070
10°	2019221
15°	805120
20°	322838
25°	154600
30°	80155
35°	42341
40°	23507
45°	14513
50°	9978
55°	6709
60°	5131
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264948

CATALOG NUMBER: LD2B20D010 EU2B2010SP159027 2LBLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	607.0	46.7
10°-20°	478.9	36.8
20°-30°	141.3	10.9
30°-40°	47.0	3.6
40°-50°	17.7	1.4
50°-60°	7.8	0.6
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1227.2	94.3
0°-40°	1274.2	97.9
0°-60°	1299.7	99.9
0°-90°	1301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9309	
5°	7548	607
15°	1576	479
25°	284	141
35°	70	47
45°	21	18
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264948

CATALOG NUMBER: LD2B20D010 EU2B2010SP159027 2LBLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9309.2
2.5°	8934.0
5°	7547.9
7.5°	5815.3
10°	4030.6
12.5°	2579.4
15°	1576.3
17.5°	961.4
20°	614.9
22.5°	411.7
25°	284.0
27.5°	200.6
30°	140.7
32.5°	99.0
35°	70.3
37.5°	49.5
40°	36.5
42.5°	28.7
45°	20.8
47.5°	18.2
50°	13.0
52.5°	10.4
55°	7.8
57.5°	7.8
60°	5.2
62.5°	2.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)