

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224935

Luminaire Tested: **LSRWM2B05FL408030D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05FL408030D010 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 766.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224935

CATALOG NUMBER: LSRWM2B05FL408030D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224935

CATALOG NUMBER: LSRWM2B05FL408030D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	94		96	94	93
3	106	100	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	94	90	87		92	89	86		91	88	85		89	86	84
5	98	91	86	83		96	90	86	82		89	85	82		87	84	81		86	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		82	77	74		80	77	74		79	76	74
8	88	80	75	72		87	79	75	72		78	74	71		77	74	71		77	73	71
9	85	77	72	69		84	76	72	69		75	71	68		75	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	69	66		72	68	66		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	710509
5°	695609
10°	612637
15°	480651
20°	319212
25°	183222
30°	91914
35°	42416
40°	17242
45°	7724
50°	4037
55°	2499
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224935

CATALOG NUMBER: LSRWM2B05FL408030D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.4	21.3
10°-20°	324.4	42.4
20°-30°	201.6	26.3
30°-40°	60.8	7.9
40°-50°	12.4	1.6
50°-60°	3.2	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	689.4	90.0
0°-40°	750.2	97.9
0°-60°	765.8	100.0
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1834	
5°	1789	163
15°	1199	324
25°	429	202
35°	90	61
45°	14	12
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224935

CATALOG NUMBER: LSRWM2B05FL408030D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1834.3
1°	1828.3
2°	1820.2
3°	1814.2
4°	1805.3
5°	1789.0
6°	1763.1
7°	1727.5
8°	1676.3
9°	1618.4
10°	1557.6
11°	1493.1
12°	1425.6
13°	1355.1
14°	1278.0
15°	1198.6
17.5°	985.7
20°	774.4
22.5°	587.4
25°	428.7
27.5°	302.6
30°	205.5
32.5°	135.0
35°	89.7
37.5°	55.6
40°	34.1
42.5°	22.3
45°	14.1
47.5°	8.9
50°	6.7
52.5°	4.5
55°	3.7
57.5°	2.2
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224935

CATALOG NUMBER: LSRWM2B05FL408030D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)