

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264063

Luminaire Tested: **LD2B20D010 EU2B2010SP158035 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158035 2LBDC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1770.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264063

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264063

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8351924
5°	6694493
10°	2921873
15°	905485
20°	315645
25°	139412
30°	63121
35°	32824
40°	18742
45°	8861
50°	5603
55°	3097
60°	1776
65°	2101
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264063

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1026.5	58.0
10°-20°	562.2	31.8
20°-30°	128.1	7.2
30°-40°	36.9	2.1
40°-50°	11.4	0.6
50°-60°	3.4	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1716.8	97.0
0°-40°	1753.7	99.1
0°-60°	1768.4	99.9
0°-90°	1770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16929	
5°	13518	###
15°	1773	562
25°	256	128
35°	54	37
45°	13	11
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264063

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	16928.6
1°	16717.9
2°	16280.2
3°	15600.9
4°	14667.2
5°	13517.5
6°	12108.0
7°	10533.2
8°	8889.3
9°	7298.2
10°	5832.4
11°	4591.8
12°	3614.6
13°	2844.4
14°	2246.9
15°	1772.8
16°	1398.6
17°	1113.4
18°	895.5
19°	728.4
20°	601.2
22.5°	388.7
25°	256.1
26°	216.1
27°	183.5
28°	154.4
29°	129.0
30°	110.8
32.5°	76.3
35°	54.5
37.5°	40.0
40°	29.1
42.5°	20.0
45°	12.7
47.5°	9.1
50°	7.3
52.5°	5.4
55°	3.6
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8



TEST NUMBER: P264063

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)