

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223430

Luminaire Tested: **LSRWM2B05NFL258030D010 2LBDLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223430  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B05NFL258030D010 2LBDLC\*MB  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 707.0 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223430

CATALOG NUMBER: LSRWM2B05NFL258030D010 2LBDLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P223430

CATALOG NUMBER: LSRWM2B05NFL258030D010 2LBDLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 113 | 112 | 110 |  | 113 | 111 | 110 | 108 |  | 107 | 106 | 105 |  | 104 | 103 | 102 |  | 100 | 100 | 99  |
| 2   | 112 | 109 | 106 | 104 |  | 110 | 107 | 104 | 102 |  | 104 | 102 | 100 |  | 101 | 99  | 98  |  | 98  | 97  | 96  |
| 3   | 109 | 105 | 101 | 99  |  | 107 | 103 | 100 | 98  |  | 101 | 98  | 96  |  | 99  | 97  | 95  |  | 96  | 95  | 93  |
| 4   | 106 | 101 | 97  | 95  |  | 104 | 100 | 97  | 94  |  | 98  | 95  | 93  |  | 96  | 94  | 92  |  | 95  | 93  | 91  |
| 5   | 103 | 98  | 94  | 91  |  | 102 | 97  | 94  | 91  |  | 95  | 92  | 90  |  | 94  | 91  | 89  |  | 93  | 90  | 89  |
| 6   | 101 | 95  | 91  | 89  |  | 99  | 94  | 91  | 88  |  | 93  | 90  | 88  |  | 92  | 89  | 87  |  | 91  | 88  | 87  |
| 7   | 98  | 92  | 89  | 86  |  | 97  | 92  | 88  | 86  |  | 91  | 88  | 85  |  | 90  | 87  | 85  |  | 89  | 86  | 85  |
| 8   | 96  | 90  | 86  | 84  |  | 95  | 90  | 86  | 84  |  | 89  | 86  | 83  |  | 88  | 85  | 83  |  | 87  | 85  | 83  |
| 9   | 94  | 88  | 84  | 82  |  | 93  | 88  | 84  | 82  |  | 87  | 84  | 82  |  | 86  | 83  | 81  |  | 85  | 83  | 81  |
| 10  | 92  | 86  | 82  | 80  |  | 91  | 86  | 82  | 80  |  | 85  | 82  | 80  |  | 84  | 82  | 80  |  | 84  | 81  | 79  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1624684 |
| 5°  | 1500089 |
| 10° | 1015359 |
| 15° | 345430  |
| 20° | 126877  |
| 25° | 67271   |
| 30° | 34574   |
| 35° | 16125   |
| 40° | 5259    |
| 45° | 2684    |
| 50° | 1265    |
| 55° | 473     |
| 60° | 542     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P223430

CATALOG NUMBER: LSRWM2B05NFL258030D010 2LBDLC\*MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 328.2  | 46.4      |
| 10°-20°   | 275.9  | 39.0      |
| 20°-30°   | 75.7   | 10.7      |
| 30°-40°   | 22.1   | 3.1       |
| 40°-50°   | 4.1    | 0.6       |
| 50°-60°   | 0.9    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 679.8  | 96.2      |
| 0°-40°    | 701.9  | 99.3      |
| 0°-60°    | 706.9  | 100.0     |
| 0°-90°    | 707.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 707.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4194 |      |
| 5°  | 3858 | 328  |
| 15° | 861  | 276  |
| 25° | 157  | 76   |
| 35° | 34   | 22   |
| 45° | 5    | 4    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P223430

CATALOG NUMBER: LSRWM2B05NFL258030D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4194.4 |
| 1°    | 4170.0 |
| 2°    | 4126.8 |
| 3°    | 4064.8 |
| 4°    | 3979.9 |
| 5°    | 3858.0 |
| 6°    | 3691.6 |
| 7°    | 3483.3 |
| 8°    | 3229.2 |
| 9°    | 2929.0 |
| 10°   | 2581.5 |
| 11°   | 2200.6 |
| 12°   | 1804.3 |
| 13°   | 1426.2 |
| 14°   | 1103.8 |
| 15°   | 861.4  |
| 17.5° | 486.1  |
| 20°   | 307.8  |
| 22.5° | 219.4  |
| 25°   | 157.4  |
| 27.5° | 111.4  |
| 30°   | 77.3   |
| 32.5° | 54.3   |
| 35°   | 34.1   |
| 37.5° | 13.9   |
| 40°   | 10.4   |
| 42.5° | 7.7    |
| 45°   | 4.9    |
| 47.5° | 2.8    |
| 50°   | 2.1    |
| 52.5° | 1.4    |
| 55°   | 0.7    |
| 57.5° | 0.7    |
| 60°   | 0.7    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P223430

CATALOG NUMBER: LSRWM2B05NFL258030D010 2LBDLC\*MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |     |
|-------|-----|
| 85°   | 0.0 |
| 87.5° | 0.0 |



(END OF REPORT)