

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL558035D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14809)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL558035D010 2LBDL*B
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 675.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	63		70	66	62		69	65	62
8	79	69	63	59		78	69	63	59		67	62	59		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	71	62	56	52		70	61	56	52		60	55	52		60	55	52		59	55	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	321342
5°	319265
10°	297351
15°	260777
20°	225270
25°	191598
30°	151982
35°	104881
40°	65835
45°	39277
50°	22778
55°	11480
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	11.3
10°-20°	181.2	26.9
20°-30°	204.0	30.2
30°-40°	140.2	20.8
40°-50°	58.2	8.6
50°-60°	15.0	2.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.5	68.4
0°-40°	601.7	89.1
0°-60°	674.9	100.0
0°-90°	675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	830	
5°	821	76
15°	650	181
25°	448	204
35°	222	140
45°	72	58
55°	17	15
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	829.6
2.5°	828.6
5°	821.1
7.5°	796.6
10°	756.0
12.5°	705.0
15°	650.3
17.5°	594.6
20°	546.5
22.5°	499.3
25°	448.3
27.5°	396.4
30°	339.8
32.5°	279.4
35°	221.8
37.5°	172.7
40°	130.2
42.5°	98.2
45°	71.7
47.5°	51.9
50°	37.8
52.5°	26.4
55°	17.0
57.5°	5.7
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)