

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225366

Luminaire Tested: **LD2B20D010 EU2B20FL408035 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225366  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20FL408035 2LBDC\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1640.1 lumens  
Efficiency: N/A  
Efficacy: 78.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225366

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P225366

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |
| 2   | 110 | 106 | 102 | 99  |  | 108 | 104 | 101 | 98  |  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 94  | 92  |
| 3   | 105 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 92  | 90  | 88  |
| 4   | 101 | 95  | 90  | 87  |  | 100 | 94  | 90  | 86  |  | 92  | 88  | 85  |  | 90  | 87  | 85  |  | 88  | 86  | 84  |
| 5   | 98  | 91  | 86  | 82  |  | 96  | 90  | 85  | 82  |  | 88  | 84  | 81  |  | 86  | 83  | 80  |  | 85  | 82  | 80  |
| 6   | 94  | 87  | 82  | 78  |  | 93  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 83  | 80  | 77  |  | 82  | 79  | 76  |
| 7   | 90  | 83  | 78  | 74  |  | 89  | 82  | 77  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 73  |  | 79  | 76  | 73  |
| 8   | 87  | 79  | 74  | 71  |  | 86  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 9   | 84  | 76  | 71  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  | 70  | 67  |
| 10  | 81  | 73  | 68  | 65  |  | 80  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  |  | 71  | 67  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1484813 |
| 5°  | 1457746 |
| 10° | 1295876 |
| 15° | 1019167 |
| 20° | 678160  |
| 25° | 389351  |
| 30° | 196664  |
| 35° | 92539   |
| 40° | 37215   |
| 45° | 18461   |
| 50° | 10124   |
| 55° | 7091    |
| 60° | 6507    |
| 65° | 3849    |
| 70° | 4757    |
| 75° | 3143    |
| 80° | 4684    |
| 85° | 0       |



TEST NUMBER: P225366

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 343.4  | 20.9      |
| 10°-20°   | 688.4  | 42.0      |
| 20°-30°   | 428.3  | 26.1      |
| 30°-40°   | 131.7  | 8.0       |
| 40°-50°   | 28.9   | 1.8       |
| 50°-60°   | 10.3   | 0.6       |
| 60°-70°   | 5.2    | 0.3       |
| 70°-80°   | 3.0    | 0.2       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1460.1 | 89.0      |
| 0°-40°    | 1591.8 | 97.1      |
| 0°-60°    | 1631.0 | 99.4      |
| 0°-90°    | 1640.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1640.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3833 |      |
| 5°  | 3749 | 343  |
| 15° | 2542 | 688  |
| 25° | 911  | 428  |
| 35° | 196  | 132  |
| 45° | 34   | 29   |
| 55° | 10   | 10   |
| 65° | 4    | 5    |
| 75° | 2    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P225366

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3833.3 |
| 2.5°  | 3816.4 |
| 5°    | 3749.1 |
| 7.5°  | 3578.7 |
| 10°   | 3294.7 |
| 12.5° | 2953.8 |
| 15°   | 2541.5 |
| 17.5° | 2091.3 |
| 20°   | 1645.2 |
| 22.5° | 1247.6 |
| 25°   | 911.0  |
| 27.5° | 641.7  |
| 30°   | 439.7  |
| 32.5° | 296.6  |
| 35°   | 195.7  |
| 37.5° | 117.8  |
| 40°   | 73.6   |
| 42.5° | 50.5   |
| 45°   | 33.7   |
| 47.5° | 23.1   |
| 50°   | 16.8   |
| 52.5° | 14.7   |
| 55°   | 10.5   |
| 57.5° | 8.4    |
| 60°   | 8.4    |
| 62.5° | 6.3    |
| 65°   | 4.2    |
| 67.5° | 4.2    |
| 70°   | 4.2    |
| 72.5° | 4.2    |
| 75°   | 2.1    |
| 77.5° | 2.1    |
| 80°   | 2.1    |
| 82.5° | 2.1    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)