

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224907

Luminaire Tested: **LSRWM2B05FL409035D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05FL409035D010 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 641.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224907

CATALOG NUMBER: LSRWM2B05FL409035D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224907

CATALOG NUMBER: LSRWM2B05FL409035D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	94		96	94	93
3	106	100	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	94	90	87		92	89	86		91	88	85		89	86	84
5	98	91	86	83		96	90	86	82		89	85	82		87	84	81		86	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		82	77	74		80	77	74		79	76	74
8	88	80	75	72		87	79	75	72		78	74	71		77	74	71		77	73	71
9	85	77	72	69		84	76	72	69		75	71	68		75	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	69	66		72	68	66		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	594537
5°	582111
10°	512655
15°	402213
20°	267109
25°	153347
30°	76885
35°	35512
40°	14461
45°	6464
50°	3375
55°	2093
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224907

CATALOG NUMBER: LSRWM2B05FL409035D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	21.3
10°-20°	271.5	42.4
20°-30°	168.7	26.3
30°-40°	50.9	7.9
40°-50°	10.4	1.6
50°-60°	2.7	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	576.9	90.0
0°-40°	627.8	97.9
0°-60°	640.9	100.0
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1535	
5°	1497	137
15°	1003	271
25°	359	169
35°	75	51
45°	12	10
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224907

CATALOG NUMBER: LSRWM2B05FL409035D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1534.9
1°	1530.0
2°	1523.1
3°	1518.2
4°	1510.7
5°	1497.1
6°	1475.4
7°	1445.6
8°	1402.7
9°	1354.3
10°	1303.4
11°	1249.4
12°	1192.9
13°	1134.0
14°	1069.4
15°	1003.0
17.5°	824.9
20°	648.0
22.5°	491.6
25°	358.8
27.5°	253.2
30°	171.9
32.5°	113.0
35°	75.1
37.5°	46.6
40°	28.6
42.5°	18.6
45°	11.8
47.5°	7.4
50°	5.6
52.5°	3.7
55°	3.1
57.5°	1.9
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224907

CATALOG NUMBER: LSRWM2B05FL409035D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)