

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223272

Luminaire Tested: **LD2B20D010 EU2B20NFL258035 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1787.9 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223272

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223272

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	104	102	104	102	100		101	99	98		98
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		96
4	106	101	97	95	104	100	97	94	98	95	93		96	94	92		95
5	103	98	94	91	102	97	94	91	95	92	90		94	91	89		93
6	101	95	91	89	99	94	91	88	93	90	88		92	89	87		91
7	98	92	89	86	97	92	88	86	91	88	85		90	87	85		89
8	96	90	86	84	95	90	86	84	89	86	83		88	85	83		87
9	94	88	84	82	93	88	84	82	87	84	82		86	83	81		85
10	92	86	82	80	91	86	82	80	85	82	80		84	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4108540
5°	3793499
10°	2567720
15°	873560
20°	320860
25°	170101
30°	87441
35°	40808
40°	13349
45°	6738
50°	3194
55°	1216
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223272

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	829.9	46.4
10°-20°	697.8	39.0
20°-30°	191.5	10.7
30°-40°	55.8	3.1
40°-50°	10.3	0.6
50°-60°	2.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.2	96.2
0°-40°	1775.0	99.3
0°-60°	1787.7	100.0
0°-90°	1787.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1787.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10607	
5°	9756	830
15°	2178	698
25°	398	191
35°	86	56
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223272

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10606.9
1°	10545.3
2°	10436.1
3°	10279.4
4°	10064.5
5°	9756.3
6°	9335.4
7°	8808.9
8°	8166.1
9°	7407.1
10°	6528.3
11°	5565.0
12°	4562.9
13°	3606.7
14°	2791.3
15°	2178.4
17.5°	1229.2
20°	778.4
22.5°	554.7
25°	398.0
27.5°	281.8
30°	195.5
32.5°	137.4
35°	86.3
37.5°	35.2
40°	26.4
42.5°	19.4
45°	12.3
47.5°	7.0
50°	5.3
52.5°	3.5
55°	1.8
57.5°	1.8
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223272

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)