

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223273

Luminaire Tested: **LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1635.3 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223273

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223273

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	113	112	110	113	111	110	108		107	106	105			104	103	102			97
2	112	109	106	104	110	107	104	102		104	102	100			101	99	98			95
3	109	105	101	99	107	103	100	98		101	98	96			99	97	95			92
4	106	101	97	95	104	100	97	94		98	95	93			96	94	92			90
5	103	98	94	91	102	97	94	91		95	92	90			94	91	89			88
6	101	95	91	89	99	94	91	88		93	90	88			92	89	87			86
7	98	92	89	86	97	92	88	86		91	88	85			90	87	85			84
8	96	90	86	84	95	90	86	84		89	86	83			88	85	83			82
9	94	88	84	82	93	88	84	82		87	84	82			86	83	81			80
10	92	86	82	80	91	86	82	80		85	82	80			84	82	80			79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3757876
5°	3469724
10°	2348562
15°	799013
20°	293490
25°	155570
30°	79972
35°	37309
40°	12237
45°	6190
50°	2892
55°	1081
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223273

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	759.1	46.4
10°-20°	638.2	39.0
20°-30°	175.1	10.7
30°-40°	51.1	3.1
40°-50°	9.4	0.6
50°-60°	2.1	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1572.4	96.2
0°-40°	1623.5	99.3
0°-60°	1635.1	100.0
0°-90°	1635.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1635.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9702	
5°	8924	759
15°	1992	638
25°	364	175
35°	79	51
45°	11	9
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223273

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	9701.6
1°	9645.2
2°	9545.4
3°	9402.0
4°	9205.5
5°	8923.6
6°	8538.6
7°	8057.0
8°	7469.1
9°	6774.9
10°	5971.1
11°	5090.0
12°	4173.5
13°	3298.8
14°	2553.1
15°	1992.5
17.5°	1124.3
20°	712.0
22.5°	507.4
25°	364.0
27.5°	257.7
30°	178.8
32.5°	125.6
35°	78.9
37.5°	32.2
40°	24.2
42.5°	17.7
45°	11.3
47.5°	6.4
50°	4.8
52.5°	3.2
55°	1.6
57.5°	1.6
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223273

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)