

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225441

Luminaire Tested: **LSR2B05FL409040D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL409040D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225441

CATALOG NUMBER: LSR2B05FL409040D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225441

CATALOG NUMBER: LSR2B05FL409040D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	95	92		103	98	94	91		96	92	90		93	91	88		91	89	87
4	101	94	90	86		99	93	89	86		91	87	85		89	86	84		88	85	83
5	97	90	85	81		95	89	84	81		87	83	80		86	82	79		84	81	79
6	93	85	80	77		92	85	80	76		83	79	76		82	78	75		81	77	75
7	89	81	76	73		88	81	76	73		80	75	72		79	75	72		78	74	72
8	86	78	73	69		85	77	73	69		76	72	69		75	72	69		75	71	68
9	83	75	70	66		82	74	69	66		73	69	66		72	69	66		72	68	65
10	80	72	67	63		79	71	66	63		70	66	63		70	66	63		69	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	522607
5°	503879
10°	443155
15°	347355
20°	240604
25°	148219
30°	82476
35°	43976
40°	21793
45°	11120
50°	6147
55°	3984
60°	1937
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225441

CATALOG NUMBER: LSR2B05FL409040D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	19.7
10°-20°	236.6	39.4
20°-30°	161.6	26.9
30°-40°	61.6	10.2
40°-50°	17.1	2.8
50°-60°	5.3	0.9
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.4	85.9
0°-40°	578.0	96.2
0°-60°	600.5	99.9
0°-90°	601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1349	
5°	1296	118
15°	866	237
25°	347	162
35°	93	62
45°	20	17
55°	6	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225441

CATALOG NUMBER: LSR2B05FL409040D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1349.2
2.5°	1334.8
5°	1295.9
7.5°	1223.2
10°	1126.7
12.5°	1004.1
15°	866.2
17.5°	724.9
20°	583.7
22.5°	458.5
25°	346.8
27.5°	254.6
30°	184.4
32.5°	131.1
35°	93.0
37.5°	65.1
40°	43.1
42.5°	28.8
45°	20.3
47.5°	14.4
50°	10.2
52.5°	7.6
55°	5.9
57.5°	4.2
60°	2.5
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)