

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223274

Luminaire Tested: **LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1649.8 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223274

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223274

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	113	112	110		113	111	110	108		107	106	105			104	103	102			97
2	112	109	106	104		110	107	104	102		104	102	100			101	99	98			95
3	109	105	101	99		107	103	100	98		101	98	96			99	97	95			92
4	106	101	97	95		104	100	97	94		98	95	93			96	94	92			90
5	103	98	94	91		102	97	94	91		95	92	90			94	91	89			88
6	101	95	91	89		99	94	91	88		93	90	88			92	89	87			86
7	98	92	89	86		97	92	88	86		91	88	85			90	87	85			84
8	96	90	86	84		95	90	86	84		89	86	83			88	85	83			82
9	94	88	84	82		93	88	84	82		87	84	82			86	83	81			80
10	92	86	82	80		91	86	82	80		85	82	80			84	82	80			79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3791188
5°	3500480
10°	2369368
15°	806110
20°	296087
25°	156980
30°	80687
35°	37640
40°	12338
45°	6245
50°	2953
55°	1081
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223274

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	765.8	46.4
10°-20°	643.9	39.0
20°-30°	176.7	10.7
30°-40°	51.5	3.1
40°-50°	9.5	0.6
50°-60°	2.2	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1586.4	96.2
0°-40°	1637.9	99.3
0°-60°	1649.6	100.0
0°-90°	1649.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1649.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9788	
5°	9003	766
15°	2010	644
25°	367	177
35°	80	52
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223274

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	9787.6
1°	9730.8
2°	9630.0
3°	9485.4
4°	9287.1
5°	9002.7
6°	8614.4
7°	8128.5
8°	7535.3
9°	6834.9
10°	6024.0
11°	5135.1
12°	4210.5
13°	3328.1
14°	2575.7
15°	2010.2
17.5°	1134.3
20°	718.3
22.5°	511.9
25°	367.3
27.5°	260.0
30°	180.4
32.5°	126.8
35°	79.6
37.5°	32.5
40°	24.4
42.5°	17.9
45°	11.4
47.5°	6.5
50°	4.9
52.5°	3.3
55°	1.6
57.5°	1.6
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223274

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)