

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B05WFL559040D010 2LBDDELETELC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B05WFL559040D010 2LBDDELETELC\*MW  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 549.1 lumens  
Efficiency: N/A  
Efficacy: 75.2 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559040D010 2LBDDELETEL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559040D010 2LBDDELETELC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 113 | 110 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 104 | 102 | 101 |  |  | 101 | 99  | 98  |  |  | 97  |
| 2   | 108 | 102 | 98  | 95  |  | 105 | 101 | 97  | 94  |  | 98  | 94  | 92  |  |  | 95  | 92  | 90  |  |  | 92  |
| 3   | 102 | 95  | 90  | 86  |  | 100 | 94  | 89  | 85  |  | 91  | 87  | 84  |  |  | 89  | 85  | 83  |  |  | 87  |
| 4   | 97  | 89  | 83  | 79  |  | 95  | 88  | 82  | 78  |  | 85  | 81  | 77  |  |  | 83  | 80  | 76  |  |  | 82  |
| 5   | 91  | 83  | 77  | 72  |  | 90  | 82  | 76  | 72  |  | 80  | 75  | 71  |  |  | 78  | 74  | 71  |  |  | 77  |
| 6   | 87  | 78  | 71  | 67  |  | 85  | 77  | 71  | 67  |  | 75  | 70  | 66  |  |  | 74  | 69  | 66  |  |  | 73  |
| 7   | 82  | 73  | 67  | 62  |  | 81  | 72  | 66  | 62  |  | 71  | 66  | 62  |  |  | 70  | 65  | 62  |  |  | 69  |
| 8   | 78  | 69  | 62  | 58  |  | 77  | 68  | 62  | 58  |  | 67  | 62  | 58  |  |  | 66  | 61  | 58  |  |  | 65  |
| 9   | 74  | 65  | 59  | 55  |  | 73  | 64  | 58  | 54  |  | 63  | 58  | 54  |  |  | 62  | 57  | 54  |  |  | 61  |
| 10  | 71  | 61  | 55  | 51  |  | 70  | 61  | 55  | 51  |  | 60  | 55  | 51  |  |  | 59  | 54  | 51  |  |  | 58  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 257546 |
| 5°  | 255886 |
| 10° | 237881 |
| 15° | 208846 |
| 20° | 180010 |
| 25° | 153946 |
| 30° | 122149 |
| 35° | 85162  |
| 40° | 53902  |
| 45° | 32867  |
| 50° | 19464  |
| 55° | 10670  |
| 60° | 2324   |
| 65° | 2108   |
| 70° | 1699   |
| 75° | 2245   |
| 80° | 1785   |
| 85° | 3555   |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559040D010 2LBDDELETELC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.1   | 11.1      |
| 10°-20°   | 145.0  | 26.4      |
| 20°-30°   | 163.6  | 29.8      |
| 30°-40°   | 113.2  | 20.6      |
| 40°-50°   | 48.2   | 8.8       |
| 50°-60°   | 14.0   | 2.5       |
| 60°-70°   | 2.1    | 0.4       |
| 70°-80°   | 1.3    | 0.2       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 369.8  | 67.3      |
| 0°-40°    | 483.0  | 88.0      |
| 0°-60°    | 545.2  | 99.3      |
| 0°-90°    | 549.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 549.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 665 |      |
| 5°  | 658 | 61   |
| 15° | 521 | 145  |
| 25° | 360 | 164  |
| 35° | 180 | 113  |
| 45° | 60  | 48   |
| 55° | 16  | 14   |
| 65° | 2   | 2    |
| 75° | 2   | 1    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B05WFL559040D010 2LBDDELETELC\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 664.9 |
| 2.5°  | 664.1 |
| 5°    | 658.1 |
| 7.5°  | 637.8 |
| 10°   | 604.8 |
| 12.5° | 564.3 |
| 15°   | 520.8 |
| 17.5° | 475.8 |
| 20°   | 436.7 |
| 22.5° | 400.0 |
| 25°   | 360.2 |
| 27.5° | 318.2 |
| 30°   | 273.1 |
| 32.5° | 224.4 |
| 35°   | 180.1 |
| 37.5° | 139.6 |
| 40°   | 106.6 |
| 42.5° | 80.3  |
| 45°   | 60.0  |
| 47.5° | 43.5  |
| 50°   | 32.3  |
| 52.5° | 23.3  |
| 55°   | 15.8  |
| 57.5° | 6.8   |
| 60°   | 3.0   |
| 62.5° | 2.3   |
| 65°   | 2.3   |
| 67.5° | 1.5   |
| 70°   | 1.5   |
| 72.5° | 1.5   |
| 75°   | 1.5   |
| 77.5° | 0.8   |
| 80°   | 0.8   |
| 82.5° | 0.8   |
| 85°   | 0.8   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)