

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL558035 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL558035 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1630.4 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558035 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558035 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	90	86		100	94	90	86		92	88	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	73		80	76	72		79	75	71		77	74	71
6	87	78	72	68		86	77	71	67		76	71	67		74	70	66		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	65	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	61	58		65	61	58
9	75	65	59	55		74	64	59	55		64	58	55		63	58	54		62	57	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	816138
5°	787916
10°	713367
15°	624934
20°	538092
25°	457434
30°	359559
35°	249860
40°	161907
45°	96904
50°	56645
55°	31740
60°	12163
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558035 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	11.4
10°-20°	433.9	26.6
20°-30°	486.1	29.8
30°-40°	334.1	20.5
40°-50°	143.5	8.8
50°-60°	43.8	2.7
60°-70°	2.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1106.6	67.9
0°-40°	1440.6	88.4
0°-60°	1627.9	99.9
0°-90°	1630.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1630.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2107	
5°	2026	187
15°	1558	434
25°	1070	486
35°	528	334
45°	177	144
55°	47	44
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558035 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2107.0
2.5°	2084.6
5°	2026.4
7.5°	1932.4
10°	1813.7
12.5°	1688.3
15°	1558.4
17.5°	1421.9
20°	1305.4
22.5°	1189.0
25°	1070.3
27.5°	944.9
30°	803.9
32.5°	660.5
35°	528.4
37.5°	414.2
40°	320.2
42.5°	239.6
45°	176.9
47.5°	129.9
50°	94.0
52.5°	64.9
55°	47.0
57.5°	31.3
60°	15.7
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)